# alber<sup>®</sup> *e-motion ® M2*5



## alber® E-MOTION® M25

 $\textbf{Electric propulsion assistance for sta} \underline{\textbf{ndard, active and comfort manual wheelchairs}}$ 

Description

E-MOTION® 🚯 Bluetcoth

**NEW**: **DuoDrive** version with specific remote control for simplified use of Cruise Mode cruise control

- Lighter: from 7.8 kg per wheel More powerful: thrust force of 40 Nm More robust: maximum user weight of 150 kg Connected with **bluetooth** and free app

- Charger with magnetic connections.

  Even more innovation and features with the **Mobility Plus** Pack, including: Speed up to 8.5 km/h Cruise control Remote control

Installation of reference 1467178 (complete fixing kit) must be carried out by Invacare® or service provider trained and approved by Invacare - E-Motion M25 wheels can be adapted to twion and E-Motion M15 bindings (change of plate required)
 2-year warranty including batteries, excluding wearing parts.

| <b>7</b> 6-1         |      | chosen with a cross in the boxes    Configuration standard   | O Options at no additional cost                                 |         |  |
|----------------------|------|--|---|---------|--|
| CODE                 | ions | DESCRIPTION  | NC: Not Compatible NC: 9999: not compatible with reference 9999 | Euros   |  |
| E-motion® M          | 25   |  |   |         |  |
| 1592520              |      | alber e-motion® M25 - 22" wheels - 6 km/h - Schwalbe Rightrun<br>black - stainless steel handrail - ECS remote control included for<br>function control  | NC : 1565894  | 7186,00 |  |
| 1592521              |      | alber e-motion® M25 - 24" wheels - 6 km/h - Schwalbe Rightrun<br>black - stainless steel handrail - ECS remote control included for<br>function control  |   | 7186,00 | An ideal solution f                                    |
| 1592522              |      | alber e-motion® M25 - 25" wheels - 6 km/h - Schwalbe Rightrun<br>black - stainless steel handrail - ECS remote control included for<br>function control  |   | 7186,00 | elderly people wit<br>loss of mobility an<br>autonomy! |
| 1594452              |      | DuoDrive remote control as a replacement for the ECS remote control (must be ordered at the same time as motorisation)   |   | 402.84  |  |
| 1594452 +<br>1592486 | 0    | DuoDrive remote control in addition to the ECS remote control (must be ordered at the same time as the motorisation)   |   | 805.69  |  |
| IMPORTANT (          | OPTI | ONS  |   |         |  |
| 1467178              |      | Complete fixing kit for e-motion M25/Twion wheels  |   | 257.82  | (Page  |
| 1584856-EM           |      | Installation of the complete mounting kit for e-motion wheels by Invacare (Required)  Average assembly time: 5 working days upon receipt of the chair (In the case of an existing chair, plan to return it to our workshops within 10 days). |   | 308.06  | 1565787  |
|                      |      | Angled or straight wheel support plates - the pair (Available if updating a wheelchair fitted with an e-motion M15)  |   | 0       | 1565788  |
| 1593206              |      | Black anti-tipper wheels with kickstand (Mandatory if originals missing )  |   | 327.01  | . ^  |

### E-MOTION®

## TO DETERMINE COMPATIBILITY:

Invacare® wheelchair (Action®, Rea®, kuschall®), please indicate the serial number of the wheelchair below to be equipped - Serial number:

Wheelchair of all other brands, please send us with this sheet the measurement of the armchair to be equipped.

#### Warning: Pair of original or Alber anti-tip wheels required.

The brakes will be adjusted to work with the motorized wheels. For your brakes to be functional with manual wheels, we advise you to equip them with the same coating as the motorized wheels.

Mobility App - the free app on your smartphone!

Included: four driving profiles to choose from, display of battery, speed and kilometers, recording of journeys made, automatic battery discharge (air transport), area for setting driving parameters for professionals

#### Pack Mobility Plus - Android and IOS

included: a maximum speed of 8.5 km/h, Cruise Mode (a real cruise control), remote control of the chair programming function of the ECS remote control

| OPTIONS      |   |                       |          |                               |
|--------------|---|-----------------------|----------|-------------------------------|
| 1592972      | ☐ Pins for quick wheel release (pair)   |                       | 101.42   |                               |
| 1457743      | Supports for anti-tipper (only when 1593206 ordered without e-motion® M25)  |                       | 154.50   |                               |
| Tyres, pair  |   | ı                     |          | A Com                         |
|              | ☐ Black Schwalbe Rightrun tyres   |                       | <b>♦</b> |                               |
| 1565894      | Schwalbe Marathon Plus Evolution tyres, black, SmartGuard puncture protection   |                       | 63.51    | 1565894                       |
| 1592532      | ☐ Pro Speed 1" tire, black (+300g per wheel)  | NC : 1592520, 1592522 | 124.17   | 1592532                       |
| 1592533      | ☐ 1" 3/8 tires with anti-puncture insert, black (+500g per wheel)   | NC : 1592522          | 24.64    | 170                           |
| Handrims - : | sold by 2 if taken with the motorization  |                       |          | 1592533                       |
|              | ☐ Stainless steel handrims  |                       | <b>*</b> |                               |
| 1592527      | ☐ Stainless steel handrims with non-slip coating (+250g per wheel)  | NC : 1592522          | 174.41   |                               |
| 1592528      | ☐ Carbolife Curve L handrims, black aluminum  | NC: 1592520           | 397.16   | 1592527                       |
| 1592529      | ☐ Carbolife Quadro Tetra Gripp handrims, aluminum   | NC : 1592520, 1592522 | 457.82   | 1552527                       |
| Handrim co   | vering, for standard stainless steel - sold by 2 if taken with the motoriz  | ation                 | 1        |                               |
| 1592425      | Removable non-slip grips, 22" wheel, sold individually Quantity desired   |                       | 61.61    | 1592528 1592529               |
| 1592421      | Removable non-slip grips, 24" wheel, sold individually Quantity desired   |                       | 61.61    |                               |
| 1592426      | Removable non-slip grips, 25" wheel, sold individually Quantity desired   |                       | 61.61    |                               |
| Spoke prote  | ectors - sold by 2 if taken with the motorization   | ,                     | <u>'</u> |                               |
| 1592266      | 22" "Comic" design spoke guards, sold individually Quantity desired   |                       | 71.09    | 1592425<br>1592421            |
| 1592268      | 24" "Sphere" design spoke guards, sold individually Quantity desired  |                       | 71.09    | 1592426                       |
| 1592269      | 25" "Sphere" design spoke guards, sold individually Quantity desired  |                       | 71.09    |                               |
| 1592553      | 24" transparent spoke guards, individually Quantity desired   |                       | 71.09    | 1952268<br>1952266<br>1592269 |
| Other Optio  |   | 1                     | I        | _                             |
| 1592523      | Warranty extension for an additional 12 months on the Lithiumion battery pack   |                       | 131.75   |                               |
| 1593388      | ☐ Magnetic holder for remote control or smartphone  |                       | 165.88   | 1593388                       |
| 1592485      | ☐ ECS remote control protective cover   |                       | 52.13    |                               |
| 1467780      | ☐ Extended brake pads   |                       | 38.86    |                               |
| 1591362      | ☐ Axle for wheel transport  |                       | 52.13    |                               |
| 1565005      | Original manual wheel adaptation kit  TIP: for perfect compatibility of the brakes with the manual wheels, we advise you to equip them with the same coating as the motorized wheels. |                       | 198.10   | 1592485<br>1591362            |